






Components



1.Cabinet profiles : L/R	10. Front fixing-brackets screw (Ø4x17)
2.89 Drawer profiles : L/R	11. Drawer back
3.121 Drawer profiles : L/R	12. Metal back height 89
4.185 Drawer profiles : L/R	13. Metal back height 121
5.Side cover plate	14. Metal back height 185
6.Bottom screw (Ø3.5x15)	15. Metal back fixed
7.89 Front fixing-brackets	16. Bottom fixing(for wide drawer)
8.121 Front fixing-brackets	17. Back fixing(for wide drawer)
9.185 Front fixing-brackets	


Item No.	Nominal length	Internal drawer length	Min.installation length of drawer
808LB-270	270mm	244mm	275mm
808LB-300	300mm	274mm	305mm
808LB-350	350mm	324mm	355mm
808LB-400	400mm	374mm	405mm
808LB-450	450mm	424mm	455mm
808LB-500	500mm	474mm	505mm
808LB-550	550mm	524mm	555mm

Drawer Back and Bottom Dimensions




Installation dimensions (mm)


Nominal slide length=NL Internal cabinet depth=LT



Drawer installation dimensions (mm)






Screw positions of the sides



Drawer installation dimensions (mm)


LW=Internal cabinet width




808 Series slender metal drawer

Assembly removal and adjustment


Drawer assembly




Bottom assembly




Back assembly




89 Front assembly




121 Front assembly




Click




Adjustment



Up&down adjustment




Left&right adjustment




Front slope angle adjustment


Removal



Tip up the cover and pull out



Removal drawer front




Removal drawer


808 Series slender metal drawer

Assembly removal and adjustment



Drawer assembly




Bottom assembly




Back assembly




Front assembly




Click




Adjustment



Up&down adjustment




Left&right adjustment




Front slope angle adjustment


Removal



Tip up the cover and pull out




Removal drawer front



Removal drawer

Components




1. Cabinet profiles: L/R	10. 808-89-2 Front Fixing brackets L/R	Item No.	Nominal length	Internal drawer length	Min. installation length of drawer
2. 89 Drawer profiles: L/R	11. 808-121-2 Front Fixing brackets L/R				
3. 121 Drawer profiles: L/R	12. 808-185-2 Front Fixing brackets L/R	808LB-270	270mm	234mm	275mm
4. 185 Drawer profiles: L/R	13. 808-1 Front section	808LB-300	300mm	264mm	305mm
5. Side cover plate	14. Cross square rail	808LB-350	350mm	314mm	355mm
6. Bottom & Back screw (Ø3.5x15)	15. 808-2 Front section	808LB-400	400mm	364mm	405mm
7. 808-89-1 Front Fixing brackets L/R	16. 808 Glass Front (89/121/185)	808LB-450	450mm	414mm	455mm
8. 808-121-1 Front Fixing brackets L/R	17. 808 Front section Screw (Ø4x30/Ø4x17)	808LB-500	500mm	464mm	505mm
9. 808-185-1 Front Fixing brackets L/R	18. 808 Bottom fixed	808LB-550	550mm	514mm	555mm

Drawer Back and Bottom Dimensions

Back 		Metal Back L=LW-42 		Drawer Bottom L=NL-20 		KB Cabinet width LW Internal cabinet width NL Nominal length 	
Type	89 121 185	KB ≥ 800mm		Metal back fixed			
H (mm)	59 91 155						

Installation dimensions (mm)


Nominal slide length=NL Internal cabinet depth=LT



Accessories cutting (mm)




14. 808-1 Front section L=LW-87		KB ≥ 800mm
16. 808-2 Front section L=LW-87		KB ≥ 800mm
17. 808 Glass Front (89/121/185) L=LW-55		
15. Cross square rail L=LW-55		

Screw positions of the sides



Drawer installation dimensions (mm)


LW=Internal cabinet width



808 Inner series slender metal drawer

Assembly removal and adjustment


808-89 Inner drawer front assembly




808 Series slender metal drawer

Assembly removal and adjustment


808-89 Inner drawer glass front assembly




808-121 Inner drawer front assembly



808-121 Inner drawer glass front assembly



808-185 Inner drawer front assembly



808-185 Inner drawer glass front assembly

